

SafePace 100 Radar Speed Sign



The portable SafePace 100 is the radar speed sign that fits your budget. This compact radar speed sign offers exceptional visibility and power efficiency in a lightweight and portable solution. Featuring the options you need at remarkably affordable pricing, the SafePace 100 is the sign you'll want to use again and again to keep your neighborhoods safe.

Features

- Affordable: Priced low enough for any budget.
- Portable: At 21 lbs, the lightweight sign is quick and simple to transport and can be mounted in minutes.
- **Energy Efficient**: The ultra low power sign utilizes the most power-efficient radar technology available. The sign can function up to four weeks autonomously with optional battery power.
- Optimal Visibility: Unique light enhancing, anti-glare lens system as well as automatic ambient light adjustment provide brilliant visibility even in poor lighting conditions.
- User Friendly Software Interface: Easy-to-use mangement

Ideal for use in:

- Residential neighborhoods
- **Private communities**
- School zones
- **Shopping centers**
- **Corporate campuses**
- **Construction zones**

software lets you set sign parameters, download traffic data, and generate statistical reports.

On-Sign Programming:

Commonly used settings, such as display speed range and digit/ strobe flashing threshold speed, can be programmed directly on

sign with a convenient on-board switch.



 Vandalism Resistant: With a 1/4" durable aluminum protective cover

and individual optical lenses shielding each LED, the sign is well protected against theft or vandalism.



Individual Protective Lenses Close-up View of Sign Digit

· Stealth Mode:

Collect baseline traffic data while speed display appears blank to motorists.

• Speed Violator Strobe: Programmable flashing strobe to alert speeding drivers comes standard with every sign.




Data Collection, Analysis & Reporting

Accurate Traffic Statistics at Your Fingertips


With the SafePace 100 data collection feature, capture important traffic data such as vehicle count, speed, date and time. Stored data can be easily downloaded and generated into statistical reports and charts for analysis. Data can be stored by location, making the SafePace 100 the perfect choice when selecting a radar sign with data collection for use in single or multiple locations.

Location: Traffic Logix Corp Address: 3 Harriett Lane, Spring Valley, NY, 10977 Speed Limit: 25						Data Session: Report Period Total Vehicle	4/4/20	Demo Statistics 4/4/2011 to 4/10/2011 ount: 23,966	
Hour	Total Vehicles	Average Vehicles	Total Violations	%. Violations	Min. Speed	Max. Speed	Avg. Speed	85% Speed	
00-01	163	23	161	99 %	18	43	32	32	
01-02	95	14	95	100 %	28	43	32	.37	
02.03	57	8	52	92 %	8	38	30	32	
03.04	36		33	91 %	18	38	32	37	
04-05	34	5	24	76 %	8	38	28	37	
05-06	98	14	65	74 %	13	53	30	32	
06-07	290	41	207	75 %	13	43	29	32	
07-08	926	132	703	62 %	8	43	30	32	
08-09	1,524	218	1,274	86 %	8	48	31	.32	
09-10	1,536	219	1,180	80 %	. 8	48	29	32	
10-11	1,442	206	1,172	83 %	13	48	30	32	
11-12	1,535	219	1,271	84 %	8	48	30	32	
12-13	1,661	237	1,398	85 %	8	48	30	32	
13-14	1,660	237	1,337	81 %	.8	-43	29	32	

Traffic Statistics Report



Average Vehicle Count



Period Comparison Graph

- Traffic data collected and stored by location
- Statistical reports & charts
 - Summary report
 - Weekly report
 - Period comparison report
 - Variety of report paramaters including:
 - Average/total vehicle count, speed & number of violations
 - Percentage of speed violations
 - 85th percentile speed
 - Minimum & maximum speed
 - Vehicle count by speed
 - Reports can be printed directly or exported into CSV format, MS Excel, Adobe Acrobat PDF, HTML, and Bitmap image formats





Sign Options

Data Collection: Built-in data engine collects traffic statistics including vehicle speed and count, allowing you to create valuable reports for analysis

Universal Mounting Bracket: Optional bracket makes mounting quick and easy, allowing you to use one sign at multiple locations. Bracket locks and unlocks with the turn of a key.

Battery Power: Lithium ion batteries offers extended operation with choice of 9.6V,

Folding Sign Plate

10Ah battery for two week performance or 12.8V, 15Ah battery for four week performance before recharge under normal operating conditions.

Solar Power: Complete and compact solar power system available.

Folding Sign Plate: Sign is available with smaller "Your Speed" sign plate that folds compactly for convenient relocation.

Specifications

Sign size with full "Your Speed" sign plate: 23.0" (w) x 29.0" (h)

Sign size with foldable "Your Speed" sign

plate: 21.5" (w) x 30.3" (h)


Digit height: 11.0"

· Sign depth: 3.0"

 Protective aluminum cover thickness: 0.25"

• Range: 300-400 ft

 Sign weight: 21.0 lbs with **AC Power**



• Operating temperature: -40F - 185F







Universal mounting bracket