

NEX10® CONNECTOR

Miniature Low PIM RF Coax Connector System

- » Space saving miniaturized interconnection
- » Excellent Passive Intermodulation
- » Quick lock & Screw coupling
- » Superior RF performance





NEX10® CONNECTOR

Miniature Low PIM RF Coax Connector System

The NEX10[®] is a new small coaxial connector system, offering low PIM and ruggedized design in a compact size, to meet the upcoming space reduction requirements of small cells. As the telecommunications industry moves towards the small cell approach, the radio and antenna become smaller and ask for a small sized, high performing coaxial RF connector.



Product features

- » Small size of 12.7 mm flange height
- » Low PIM, independent of applied torque
- » One interface but two coupling mechanism
 - Screw and Quick lock coupling
- » Robust design for outdoor use
- » High protection of all contact areas
- » Optimized for semiflex and ¼" corrugated cables

Characteristics

- » Impedance: 50Ω
- » Excellent RF performance up to 20 GHz
- » Superior passive intermodulation values
 - better than -166dBc
- » Return loss: ≥ 36dB up to 6 GHz
- » Power rating typ. 100W @ 2 GHz @ 85°C
- » IP 68 watertight solution





















APPLICATIONS

- » Small Cell and MIMO
- » Distributed Antenna Systems (DAS) / In-building antennas
- » Antennas, radios and filter output
- » Applications requiring PIM stability in a compact size
- » Multi coax / Blind mate applications



Product portfolio

	Picture	Part number (P/N)	Cable type	Description	Packaging	Plating
Cable types		5553.NEX.1410.075	Flexiform 402 UT 141	Straight Cable Plug Screw	Bulk packaging	5 = White bronze
		5562.NEX.1410.085	1/4" corrugated cable	Straight Cable Plug Screw	Bulk packaging	5 = White bronze
		5552.NEX.1410.075	Flexiform 402 UT 141	Straight Cable Plug Quick lock	Bulk packaging	5 = White bronze
Flange types		5550.NEX.2018.195	-	Straight 4-hole Flange Jack	Tray packaging	5 = White bronze
Adapters		5554.NEX.8910.005	-	Measuring Adapter NEX10(m) - RPC-3.50(f)	Bulk packaging	5 = White bronze
		5555.NEX.8910.005	-	Measuring Adapter NEX10(f) - RPC-3.50(m)	Bulk packaging	5 = White bronze





EUROPE

IMS Connector Systems GmbH Obere Hauptstraße 30 DE-79843 Löffingen

Phone +49 (0) 7654 901-100 Fax +49 (0) 7654 901-199 sales@imscs.com

AMERICAS

IMS Connector Systems Inc. 22305 Golden Canyon Circle Chatsworth US-CA 91311

Phone +1 (0) 214 704-1115

salesusa@imscs.com

APAC

IMS Connector Systems Ltd No 35, Huo Ju Road SND Science & Technology Parl CN-Suzhou 215011

Phone +86 (0) 512 6808-1816 Fax +86 (0) 512 6825-2388 sales@imscscn.com



HEADQUARTERS, GERMANY IMS Connector Systems GmbH Obere Hauptstraße 30 DE-79843 Löffingen

Phone +49 (0) 7654 901-100 Fax +49 (0) 7654 901-199

sales@imscs.com www.imscs.com

