

1	2	3	4
Product P/N	Connector P/N	Position NO	Cable
1IC03622051706	40002153-01-001	2	900-00201-00112 NOUL 2C*26AWG TPU OD3.1
1IC03622051706	40003153-01-001	3	900-00301-00093 NOUL 3C*26AWG TPU OD3.1
1IC03622051708	40004153-01-001	4	900-00401-00146 NOUL 4C*14mm ² TPU OD3.7
1IC03622051709	40005153-01-001	5	900-00501-00056 NOUL 5C*14mm ² TPU OD3.7
1IC03622051710	40006153-01-001	6	900-00601-00062 NOUL 6C*26AWG TPU OD4.1

CABLE 1:


Pin	Color
6	VIOLET
5	GREEN
4	BLACK
3	BLUE
2	YELLOW
1	RED

Pin	Color
5	BLACK
4	WHITE
3	BROWN
2	ORANGE
1	RED


Pin	Color
4	WHITE
3	BROWN
2	ORANGE
1	RED

Pin	Color
3	BLUE
2	YELLOW
1	RED

Pin	Color
2	YELLOW
1	RED



Connector P/N See CABLE 1



Specification:

1. Operating temperature: -25°C ~ +80°C.
2. Current Rating: 2A
3. Voltage Rating: 48VAC, 60VDC.
4. Insulation resistance: 10MΩ at 300VDC.
5. Mating cycles: 200 cycles.
6. Waterproof: IP66 (Mated).
7. RoHS compliant.

3	900-00***-00***	A/R	M	Cable 2C~6C Range Maxφ4.5 0.14mm ² ~0.2mm ² Other Requirements Can Be Customized
2	504-00011-00	A/R	M	HEAT SHRINK TUBE OD1.5
1	4000*153-01-001	1	PC	Micro Series * Pin Male Connector
No.	Material No.	Q'ty	Unit	Material Description

Material List

ITEM NO.	1IC036220517**	DRAWN BY	XU	DATE	2022/05/31
DWG NO.	1IC036220517**	CHECKED BY		DATE	
CUSTOMER NO.		REV.		APPROVED BY	

UNIT:mm		TITLE	Micro series molding socket male connector
未注线性和角度尺寸公差 UNSPECIFIED TOLERANCE	SCALE N/A	SHEET	1 of 1
GB/T 1804-M	REV. C1	SIZE A4	* Inspection Item

CHOGORI
Chogori Technology Co., Ltd

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN CHOGORI PERSONNEL WITHOUT AUTHORIZATION FROM CHOGORI CORP.