
## **HEAVY DUTY GOOSENECK FLEX ARM**

95010 16" Long, 3/8-16 Female, Magnetic Base



ARM LENGTH	16" (406.4mm)
ARM MATERIAL	Steel
OUTSIDE DIAMETER	.695"
INSIDE DIAMETER	.325"
LOAD RATING	Max Load @ 90 Degrees:
	2.5 pounds
FEEL	Heavy Duty, Feels Stiff
MOUNTING STYLE	Magnetic Base, 3.0" Dia (76.2mm)
TOP FITTING	3/8-16 UNC Female Thread
BASE FITTING	3/8-16 UNC Female Thread,
	with Magnetic Base Attached
COVERING SLEEVE	PVC, Matte Black



800-346-0761

222 Cessna Street
Watertown, SD 57201
sales@moffattproducts.com

