



LED EM16-7W4040*ew*

Bulb Class: MR16



Product Description

LED EM16-7W4040*ew* delivers superior brightness, valuable energy savings and long lasting performance. This flood MR16 LED bulb is ideal for accent lighting due to its focal *Bright White Light (4000K) replacing conventional 50 Watt incandescent bulbs. Look for EM16-7W4020*ew* for Warm White (2700K), EM16-7W4000*ew* for Soft White (3000K) and EM16-7W4050*ew* for Cool White (5000K).









\$0.84 per year





Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
7 W	12V	500 lm	40°	N/A	4000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
80	71 lm/W	0.7	0.62 A	GU5.3	25,000 Hrs.

Product Features

Dimmable




Energy Efficient



Damp Rated

Product Dimensions



Product Photometric Data

