



REV.	LOOKS:	DESCRIPTION	DATE	DRAWN
01	NEW	BATCH PRODUCTION INITIAL RELEASE.	2013.05.24	郭均濤
02	△	零件規格標準・圖紙編修 (圖紙編修)	2017.05.09	何東華
03	△	依業務量標準修訂規格	2020.10.04	何東華

Dim.E	NOTE
6.00mm	03~08pins
8.50mm	09~32pins



Greenconn P/N	Customer	Remarks
GPHC204-1202A001R1BE	CO14	Automotive Connector

Ordering Information

G PHC204 - XX XX A 001 R 1 B X

No. Of Pins Per Row 03~32

Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/Tin

Color 1=Black

Standard Packing
O=Tube
Selective Packing
E=Cap+Tube
F=Cap+Tape&Reel

格稜 股份 有限 公司
Greenconn Corporation

REV. 03 UNIT. mm SCALE. 3:1 PAGE. 1/1

GENERAL TOLERANCE	X: ±0.30
X: ±5.0'	X: ±0.30
.X: ±3.0'	.X: ±0.25
.XX: ±2.0'	.XX: ±0.15
.XXX: ±1.0'	.XXX: ±0.10

DESIGNED: 何東華	DATE: 2020.10.04
CHECKED:	DATE:
CO SIGNED: 廖世瀛	DATE: 2020.10.04
APPROVED:	DATE:

DWG. NO.	PART NO.
GPHC204-CA1RB	GPHC204-XXXX A001R1BX

TITLE:
2.54 BOX HEADER
DUAL ROWS SMT TYPE
CONNECTOR

★ All materials must meet GREENCONN hazardous substances control standards.
 ★ Critical Characteristics.
 indicates product characteristics, functionalities, and manufacturing processes regarding to customer's specifications
 ☆ Safety Features indicates product characteristics, functionalities, and manufacturing processes complying to legal regulations stated by local government

Recommended P.C.Board Layout
(Tolerance: ±0.05)

