

ø37mm Spur Gear Motor Carbon - Brushed / Off-Set Shaft

MOT-RB37GM-30-12V

Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Spur - Offset Shaft
Motor Type:	Carbon - Brushed
Rated Voltage:	12V DC
Rated Speed:	173 rpm
Rated Torque:	5 kg.cm
Rated Current:	1.56 A

No-Load Speed:	200 rpm (+/- 10%)
No-Load Current:	< 250 mA
Stall Torque:	37 kg.cm
Max. Power:	19 W
Max. Efficiency:	51%
Termination Style:	Terminals





