4x Zoom, HD IP Dome Camera

- 1080p HD resolution
- 2.8mm 12mm motorized lens
- Digital wide dynamic range
- Day/Night switching for almost any lighting condition
- H.264
- PoE
- Vandal-resistant IP66 enclosure
- Indoor/outdoor



High resolution, color video in low light conditions

The MZ-HD30-8-C is a high-quality, high-resolution color video camera with a motorized zoom lens and auto-iris. It will produce high-definition video in low light conditions. The camera includes integrated IR LEDs for operation at 0 lux up to 30 meters.

This high resolution camera supports multiple streams and resolutions in H.264 codec. The zoom lens is

remotely adjustable from 2.8 to 12 mm, to provide a horizontal field-of-view of over 90 degrees.

The camera is housed in an indoor/outdoor vandal-resistant enclosure rated IK10 and IP66. It comes ready for mounting and requires only a powered Ethernet network connection.

▶ specifications

populations	
Imager	1/2.8" IMX307 CMOS
Shutter	1/25s ~ 1/100000s
Minimum Illumination	0.001 Lux Color 0 Lux (IR on) to 30m
Exposure	Auto
White Balance	Auto
Iris	Auto
Focus	Auto
Zoom Ratio	4x
View Angle	30° - 100°
Focal Length	2.8 -12 mm
F-number	F1.2
Ethernet	10/100 Mbps Ethernet (RJ-45)
Resolution	1080p, 720p, 4CIF, CIF
Compression	H.264
Frame Rate	30 FPS at 1080p
Protocols	TCP/IP, HTTP, FTP, SMTP
Weight	2.3 lbs.
Voltage Required	IEEE 802.3af compliant PoE, 12 VDC
Power Consumption	< 5 W
Operating Temperature	-30°C - 60°C
Dimensions	6.19" W x 4.86" H
Rating	IP66, IK10

▶ features



Wide dynamic range imager for quality video in challenging lighting conditions



IEEE 802.3af compliant PoE



Rated IP66 for all weather applications

▶ ordering information

MZ-HD30-8-C

►IVC camera management software

Point & click camera management & control

Robust, enterprise class software to manage and control your cameras and video from anywhere in the world.





