Panel Work Light

ENAWLL8

The Panel Work Light has a variety of features that make this light very versatile. Its 2 adjustable panels provide 180° of lighting (each) and you can direct the light wherever you need. In addition to that, both legs are adjustable so you can place it however you need and also hang it anywhere. This light is not only rechargeable but it also has a USB port out which can be used to charge other devices. This USB port feature may come in handy in emergency situations. No matter the activity, be it work, DIY project, outdoors or camping, the Panel Work Light is a great option for your lighting needs.



Provides 1100 Lumens of Light



Provides Run Time of 6 Hours



Sustains 2 Meter **Drop Test**



Water Resistant IPX4 - works after splashing water on all sides

DESIGN BENEFITS

- Durable construction for tough situations
- Adjustable handle that can be used to position the light or hang it
- 2 Adjustable panels (180 lighting each)
- Rechargeable (cable included)
- USB Port Out to charge other devices
- Panels adjust individually for maximum flexibility
- 4x Green Color LED charging indicator for 25, 50, 75, 100% charge

LIGHT AND POWER SOURCE

- √ Features LED Technology
- ✓ Operates on Li-ion Rechargeable battery

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power: Power consumption 8.7W / Battery 18650 Liion 3.7V DC

LED Specifications: LED 3.0V cc / 2900 mA

CERTIFICATES AND COMPLIANCE

EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

- *Light output measured from LED. Value is only applicable to the LED. Actual device light output
- **Endpoint determined at 1% of initial value.

Results based on: 18650 Li-lon

PERFORMANCE BENEFITS

- Powerful bright light
- 2 panels that provide 180 degrees of lighting

SPECIFICATIONS

Weight including Batteries:

462 Grams / 16.3 Ounces

Dimensions:

202 mm x 49 mm x 147 mm / 8" x 1.9" x 5.8"

NUMBER OF OPERATING MODES: 2

Mode	Lumens (lm)	Runtime (h)
High	1100	6
Low	550	