



Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!



Specifications			
<b>Gearhead Type:</b>	Planetary	<b>No-Load Speed:</b>	57 rpm (+/- 10%)
<b>Motor Type:</b>	Carbon - Brushed	<b>No-Load Current:</b>	< 1A
<b>Rated Voltage:</b>	12V DC	<b>Stall Torque:</b>	119 kg.cm *
<b>Rated Speed:</b>	47 rpm	<b>Max. Power:</b>	17.3 W
<b>Rated Torque:</b>	20 kg.cm	<b>Reduction Ratio:</b>	264:1
<b>Rated Current:</b>	2.7 A	<b>Termination Style:</b>	Terminals

\* Gearbox limitations are set at 40 kg.cm, operating past this torque limit may create premature failure.

