
BAVG2Socket

SKU:A104









Description

BAVG2Socket is a transfer line terminal suitable for RS485 line construction. The conversion head integrates the 2.54-2P terminal and the DC power input interface into a 3.96-4P specification terminal. It is convenient to access the equipment using 3.96-4P interface in the M5 hardware system. The equipped DC power interface can facilitate users to use commonly used DC adapters as power input.

Product Features

• DC power interface

RS485 transfer terminal

Includes

- 1x 120Ω plug-in resistor
- 1x 2.54-2P connection terminal
- 1x 3.96-4P connection terminal

Specification

Resources	Parameter
DC input	Voltage: 9-24V, Model: DC-IN-TH_DC-0440-2.5A-2.0
Net weight	6.7g
Gross weight	10.7g
Terminal specifications	2.54-2P+DC-0440 to 3.96-4P

Product Size

17*30*10mm

Package Size

35*36*18mm