



LED EA19-14W1100*eGV*

Bulb Class: A19



Product Description


LED EA19-14W1100*eGV* replaces conventional 100 Watt incandescent bulbs delivering more brightness (lumens) for less energy (Watts). With lower energy consumption levels you will be able to experience considerable energy savings throughout the years. EA19-14W1100*eGV* design reduces internal bulb heat providing greater durability and constant bulb performance.













Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
14 W	120 -277V	1600 lm	210°	N/A	3000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base	Lamp Lifespan
80	114.3 lm/W	0.7	N/A	GU24	15,000 Hrs.

Product Features

Energy Efficient




Damp Rated



High Output

Product Dimensions



Product Photometric Data

