THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

OPEN VIEW

2



ADHESIVE BACKING PRESSURE SENSITIVE FOAM 1.0 THICK WITH PROTECTIVE LINER.

В

11.7	

PART NAME	PANDUIT PART NUMBER (SEE NOTE 1)	LENGTH m	STATIC LOAD (SEE NOTE 2)	APPROX. WEIGHT
LATCHING	LD3**2-A	2.0±3.3mm	5.4 kg/m	.067 kg/m
DUCT	LD3**3-A	3.0±3.3mm	5.4 kg/m	.067 kg/m

NOTES: 1.SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.

2.PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE. THE SURFACE MUST BE PROPERLY PREPARED IN ACCORDANCE WITH PANDUIT RECOMMENDATIONS.

- 3.TO APPLY PART:
 - a.REMOVE PROTECTIVE LINER.
 - 6.PLACE PART IN DESIRED LOCATION.
 - C.APPLY PRESSURE TO FLAT SURFACE OF PART.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

ALL DIMENSIONS ARE IN MILLIMETERS EXCEPT WHERE NOTED.

В

								LATCHING DUCT (LD3) METRIC
								CUSTOMER DRAWING
F								TITEM REVISION NAME D34078BA/03 DATASET FILE NAME D24078BA/D3 DATASET FILE NAME
								D34078BA_LD3_METRIC/03A
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
								.XX ± .03 [0.8] ANGLES ±
	АЕС	11-06-19	BSN	BETL	ELN	F. UPDATED LENGTH TOLERANCE TO MATCH CONTROL DWG	34078-31	THIRD ANGLE PROJECTION 34078-31
F	REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE SIZE BENTZ 09-03-88 WJB FULL SHT 1 OF 1 A
						2		1