

MOT-RB37GM-150

Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Spur - Offset Shaft
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	33 rpm
Rated Torque:	21 kg.cm
Rated Current:	1.17 A

No-Load Speed:	40 rpm (+/- 10%)
No-Load Current:	< 150 mA
Stall Torque:	124 kg.cm
Max. Power:	12.7 W
Reduction Ratio:	150:1
Termination Style:	Terminals





