



# **LED** EM16-7W4000*ew*

**Bulb Class: MR16** 



### **Product Description**


**LED** EM16-7W4000*ew* delivers superior brightness, valuable energy savings and long lasting performance. This flood MR16 LED bulb is ideal for accent lighting due to its focal \*Soft White Light (3000K) replacing conventional 50 Watt incandescent bulbs. Look for EM16-7W4020*ew* for Warm White (2700K), EM16-7W4040*ew* for Bright White (4000K) and EM16-7W4050*ew* for Cool White (5000K).













# Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
7 W	12V	500 lm	40°	N/A	3000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
80	71 lm/W	0.7	0.62 A	GU5.3	25,000 Hrs.

### **Product Features**

Dimmable




**Energy Efficient** 



Damp Rated

### **Product Dimensions**



# **Product Photometric Data**

