

Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



View Alternative Solutions!

Specifications	
Gearhead Type:	Spur
Motor Type:	Carbon - Brushed
Rated Voltage:	12V DC
Rated Speed:	330 rpm
Rated Torque:	2.5 kg.cm
Rated Current:	1.6 A

No-Load Speed:	375 rpm (+/- 10%)
No-Load Current:	< 300 mA
Stall Torque:	21 kg.cm
Max. Power:	20 W
Reduction Ratio:	16:1
Termination Style:	Terminals





