## 5 WATT LED GRAY TASK LIGHT, 24"

94321 24" Long, 5 Watt LED Gray Flexible Arm Lamp, Magnetic Base



ARM LENGTH	24" (609.6mm)
ARM MATERIAL	Steel
OUTSIDE DIAMETER	.675"
COVERING SLEEVE	PVC, Gloss Gray
BULB	Installed, non integrated 5 watt (500 Lumen), PAR20 size, LED bright white bulb (40 watt equivalent)
SHADE	4.5" high, 3.5 diameter, rotates 270°,
SWITCH	Rotary style
CORD	2-wire 18 gauge SPT-2, rated 60°C, with NEMA 1- 15P 2 prong plug
APPROVALS	C-UL listed
MOUNTING	Magnetic base 100lb pull, 3" diameter
BASE	Direct mount base of arm mounts to magnetic base with two 1/4-20 socket head cap screws



800-346-0761

222 Cessna Street Watertown, SD 57201

sales@moffattproducts.com

