

## **ø42mm Planetary Gear Motor 3-Phase Brushless**

MOT-I-81535

Online ID#:

PGMBL-J42-24-10-580-C

Our BLDC Planetary Gear Motors are an inline solution providing excellent torque output and superior reliability and control.

With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!



Specifications	
Gearhead Type:	Planetary
Motor Type:	Brushless - 8 Pole
Rated Voltage:	24V DC
Rated Speed:	392 rpm
Rated Torque:	10 kg.cm
Rated Current:	3.35 A

No-Load Speed:	580 rpm (+/- 10%)
No-Load Current:	< 0.60 A
Stall Torque:	36 kg.cm
Max. Power:	53 W
Reduction Ratio:	10:1
Termination Style:	Lead Wires (26/20AWG)





