

ø30mm Spur Gear Motor Carbon - Brushed / Off-Set Shaft

MOT-RB30GM-20-24V

Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Spur - Offset Shaft
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	245 rpm
Rated Torque:	1.25 kg.cm
Rated Current:	300 mA

No-Load Speed:	325 rpm (+/- 10%)
No-Load Current:	< 150 mA
Stall Torque:	5.1 kg.cm
Max. Power:	4.23 W
Max. Efficiency:	45%
Termination Style:	Terminals





