



Note: parts in bulk,
100SET/bag

ELECTRICAR CHARACTERISTICS REQUIREMENTS:

- 1.Product must be 100% conduction,open circuit short circuit test.
- 2.Conductive resistance : 20Ω
- 3.Rated voltage: AC 60V
- 4.Withstand voltage: AC 200V
- 5.Insulation resistance:500m Ω
- 6.characteristic impedance : 50Ω
- 7.Adopt environmental protection process and meet ROHS requirements
8. Tensile test: 1.5kg~
9. The general tolerance shall prevail if no tolerance is noted

RoHS Compliant

ITEM	PART No.	VENDOR	DESCRIPTION	Q'TY	OVERALL WIRE LENGTH
5	COVER	-	RED HAT PACKING SMA	1	-
4	SMA FEMALE	-	11*1.78-ZYK-OPENING WELDING GOLD PLATING	1	-
3	HEAT SHRINK SLEEVE	-	2.0*18MM BLACK HEAT SHEINK SLEEVE	1	-
2	IPEX-1.37 CONN	-	IPEX-1.37 BRASS GOLD	1	-
1	COAXIAL CABLE	-	RG1.37 GRAY-48-TIN-FEP JACKET L=55mm	1	55
MATERIAL SPECIFICATION					

△3				DRAWN BY	CHECKED BY	APPROVED BY	CONFIRMED BY	DESCRIPTION		瀚荃股份有限公司 CviLux Corporation	CUST. CODE	
△2				LuLu	Iron	Iron	Waleed	RF CABLE			DRAWING No.	CUC
△1				08/21.20'	08/21.20'	08/21.20'	08/21.20'	SHEET: 1 OF 1		CviLux P/N	CUSTOMER P/N	
SYM	NAME	DATE	REVISIONS							DH50626A	DH-20G50012	-