


MOT-KM NJSC-12-A


Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!

| Specifications | |
|----------------|------------------|
| Gearhead Type: | Spur |
| Motor Type: | Carbon - Brushed |
| Rated Voltage: | 5V DC |
| Rated Speed: | 106 rpm |
| Rated Torque: | 250 g.cm |
| Rated Current: | 130 mA |

| No-Load Speed: | 132 rpm (+/- 10%) |
|---------------------|-------------------|
| No-Load Current: | < 45mA |
| Stall Torque: | 1,294 g.cm |
| Stall Current: | 550 mA |
| Max. Power: | 0.44 W |
| Termination Styles: | Terminals |





 $\ensuremath{\mathbb{C}}$ 2020 ISL Products International Ltd. Specifications subject to change without notice.

ISL Products International Ltd. • 235 Robbins Ln., Ste 270 • Syosset, NY 11791 • T 516-937-3475 • www.islproducts.com

