UbiBot®Wireless Muti-Sensor Device Series



PT 100

PT 100 Industrial-grade Temperature Probe is made of specially treated platinum wire wrapped around the inner surface of the probe. It can reflect the actual temperature quickly and accurately. The buttcock line is made of high temperature zone shielded fiberglass material, with a temperature range of up to 200 degrees Celsius. PT100 adopts the chip imported from Germany with high stability, and adopts three-wire connection mode to ensure the accuracy and antiinterference ability. It can connect with WS1 Pro and GS1 series.

Technical specifications Monitoring Temperature Range : -200 to 400°C

Buttcock Line Temperature Range : $-30 \sim 200^{\circ}C$ Accuracy : $\pm (2\% + 1^{\circ}C)$

Connector : Micro USB, 3.5mm Audio Output Interface : RS485 Communications Protocol : Modbus

Physical specifications

Materials : Stainless steel Size of Stainless Steel Probe : 5mm diameter x 200mm long Cable Length : 300cm IP Level : IP68

Working Voltage : DC 5-12Vpower dissipation $: \le 0.1W$

Dalian Cloud Force Technologies CO., LTD