
# NBF-SERIES NEMA ECONOMY ENCLOSURES







#### Part Number and Product Details on Page 3-4

## **Ordering Information**

- All items priced, sold and packaged in quantities of one
- Available beginning June 1, 2010
- Contact the factory for modified versions

#### **Obsolete Product Replacement Suggestions**

	Suggested	•	Suggested	Obsolete	Suggested	Obsolete	Suggested			
Obsolete Replacement		<b>Obsolete Part</b>	Replacement	Part	Replacement	Part	Replacemen			
Part Number	Part	Number	Part	Number	Part	Number	t Part			
NBB-10220	NBF-32102	NBB-10231	NBF-32204	NBB-15258	NBF-32346	NBB-22258	NBF-32046			
NBB-10221	NBF-32104	NBB-10232	NBF-32206	NBB-22220	NBF-32002	NBB-32640	NBF-32010			
NBB-10222	NBF-32106	NBB-10233	NBF-32208	NBB-22221	NBF-32004	NBB-32643	NBF-32018			
NBB-10223	NBF-32108	NBB-10258	NBF-32146	NBB-22222	NBF-32006	NBB-32647	NBF-32026			
NBB-10230	NBF-32202	NBB-10278	NBF-32246	NBB-22223	NBF-32008	NBB-32653	NBF-32032			
BUD INDUSTRIES, INC. • 4605 E. 355th Street • Willoughby,           Ohio 44094 • (440) 946-3200 • Fax (440) 951-4015           E-MAIL: saleseast@budind.com • WEB SITE: www.budind.com           BUD WEST• Phoenix, Arizona • (602) 870-8377 • Fax (602) 870-8477										
1										

### **Product Detail Information**

ABS Indoor Version Catalog			Outdoor Version Catalog		Nominal External Dimensions				Actual Internal Dimensions			
#	Catalog	Number	Number		Inches [Millimeters]				Inches			
Solid Door	Solid Door	Clear Door	Solid Door	Clear Door	A	B		D	E	F	G	Wgt. Lbs.
2001		D001	10001		<b>A</b>	Ь					U	105.
NBF- 32002	NBF- 32102	NBF- 32202	NBF- 32302	NBF- 32402	5.11 [130mm]	3.93 [100mm]	2.75 [70mm]	1.97 [50mm]	4.55	3.42	2.52	0.6
NBF- 32004	NBF- 32104	NBF- 32204	NBF- 32304	NBF- 32404	5.90 [150mm]	3.93 [100mm]	2.75 [70mm]	1.97 [50mm]	5.37	3.42	2.52	0.7
52001	52101	52201	52501	52101	[150mm]	[Toomin]	[/onnij	[Johnin]	5.57	5.12	2.52	0.7
NBF-	NBF-	NBF-	NBF-	NBF-	7.87	3.93	2.75	1.97	7 21	2.40	2.52	0.0
32006	32106	32206	32306	32406	[200mm]	[100mm]	[70mm]	[50mm]	7.31	3.42	2.52	0.8
NBF-	NBF-	NBF-	NBF-	NBF-	10.63	3.93	2.75	1.97				
32008	32108	32208	32308	32408	[270mm]	[100mm]	[70mm]	[50mm]	10.02	3.42	2.52	0.8
						1						
NBF-	NBF-	NBF-	NBF-	NBF-	5.9	5.90	3.54	2.76	5.00	5.00	2 21	0.0
32010	32110	32210	32310	32410	[150mm]	[150mm]	[90mm]	[70mm]	5.22	5.22	3.31	0.8
NBF-	NBF-	NBF-	NBF-	NBF-	7.87	5.90	3.93	2.95				
32012*	32112*	32212*	32312*	32412*	[200mm]	[150mm]	[100mm]	[75mm]	7.70	5.73	3.70	1.2
						1						
NBF-	NBF-	NBF-	NBF-	NBF-	7.08	7.08	5.90	4.72				
32014*	32114*	32214*	32314*	32414*	[180mm]	[180mm]	[150mm]	[120mm]	7.09	7.09	5.67	1.5
NBF-	NBF-	NBF-	NBF-	NBF-	11.81	7.87	5.11	4.02				
32016*	32116*	32216*	32316*	32416*	[300mm]	[200mm]	[130mm]	[102mm]	11.18	7.20	4.82	2.0
						i – – –						
NBF-	NBF-	NBF-	NBF-	NBF-	11.81	7.87	6.29	5.20				
32018	32118	32218	32318	32418	[300mm]	[200mm]	[160mm]	[132mm]	11.18	7.20	6.00	2.7
NDE	NDE	NDE	NDE	NDE	11.81	7.87	7.87	6.81				
NBF- 32020*	NBF- 32120*	NBF- 32220*	NBF- 32320*	NBF- 32420*	[300mm]	[200mm]	[200mm]	[173mm]	11.18	7.20	7.58	2.8
								<u> </u>	-	-	_	
NBF-	NBF-	NBF-	NBF-	NBF-	13.78	9.84	5.90	4.72				
32022*	32122*	32222*	32322*	32422*	[350mm]	[250mm]	[150mm]	[120mm]	12.99	9.06	5.61	3.0
					12 70	0.94	7.00	5.01				
NBF- 32024*	NBF- 32124*	NBF- 32224*	NBF- 32324*	NBF- 32424*	13.78 [350mm]	9.84 [250mm]	7.08 [180mm]	5.91 [150mm]	12.99	9.06	7.58	4.7
						[2501111]	[100mm]	[1501111]	12.77	2.00	,	
	* Non-stocking item. Contact factory for price and availability.											

N/A = Not Available.

ABS Catalog #	Indoor Version Catalog Number Outdoor Version Catalog Number			Nominal External Dimensions Inches [Milimeters]				Actual Internal Dimensions Inches			Wgt	
Solid	Solid	Clear	Solid	Clear								
Door	Door	Door	Door	Door	A	B			Ē	F	G	Lbs.
NBF- 32026	NBF- 32126	NBF- 32226	NBF- 32326	NBF- 32426	15.74 [400mm]	11.81 [300mm]	6.29 [160mm]	5.2 [132mm]	15.14	11.02	5.96	5.6
NBF- 32028*	NBF- 32128*	NBF- 32228*	NBF- 32328*	NBF- 32428*	17.71 [450mm]	13.78 [350mm]	6.29 [160mm]	5.12 [130mm]	16.65	12.64	5.96	6.9
NBF- 32030*	NBF- 32130*	NBF- 32230*	NBF- 32330*	NBF- 32430*	17.71 [450mm]	13.78 [350mm]	7.87 [200mm]	6.69 [170mm]	16.65	12.64	7.54	8.9
NBF- 32032	NBF- 32132	NBF- 32232	NBF- 32332	NBF- 32432	19.68 [500mm]	15.74 [400mm]	6.29 [160mm]	5.12 [130mm]	18.82	14.88	5.96	9.6
NBF- 32034*	NBF- 32134*	NBF- 32234*	NBF- 32334*	NBF- 32434*	19.68 [500mm]	15.74 [400mm]	7.87 [200mm]	6.69 [170mm]	18.82	14.88	7.54	10.6
NBF- 32036*	NBF- 32136*	NBF- 32236*	NBF- 32336*	NBF- 32436*	20.86 [530mm]	16.92 [430mm]	6.29 [160mm]	5.12 [130mm]	19.69	15.71	5.96	10.6
NBF- 32038	NBF- 32138	NBF- 32238	NBF- 32338	NBF- 32438	20.86 [500mm]	16.92 [430mm]	7.87 [200mm]	6.69 [170mm]	19.69	15.71	7.54	11.7
NBF- 32040*	NBF- 32140*	NBF- 32240*	NBF- 32340*	NBF- 32440*	23.62 [600mm]	19.68 [500mm]	7.08 [180mm]	5.91 [150mm]	23.58	19.69	6.71	13.9
NBF- 32042	NBF- 32142	NBF- 32242	NBF- 32342	NBF- 32442	23.62 [600mm]	19.68 [500mm]	9.84 [250mm]	8.66 [220mm]	23.62	19.69	9.47	16.1
NBF- 32044*	NBF- 32144*	NBF- 32244*	NBF- 32344*	NBF- 32444*	27.55 [700mm]	19.68 [500mm]	7.08 [180mm]	5.91 [150mm]	27.52	19.65	6.71	15.8
NBF- 32046	NBF- 32146	NBF- 32246	NBF- 32346	NBF- 32446	27.55 [700mm] [800mm]	19.68 [500mm]	9.84 [250mm]	8.66 [220mm] [257mm]	27.56	19.69	9.47	18.2
S2040         S2140         S2240         S2340         S2440         [800mm]         [600mm]         [280mm]         [257mm]         27.50         19.09         9.47         18.2           * Non-stocking item. Contact factory for price and availability.         *<												

N/A = Not Available.