



Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

| Specifications            |                  |                         |                   |
|---------------------------|------------------|-------------------------|-------------------|
| <b>Gearhead Type:</b>     | Planetary        | <b>No-Load Speed:</b>   | 176 rpm (+/- 10%) |
| <b>Motor Type:</b>        | Carbon - Brushed | <b>No-Load Current:</b> | < 0.3 A           |
| <b>Rated Voltage:</b>     | 3V DC            | <b>Stall Torque:</b>    | 1.13 kg.cm        |
| <b>Rated Speed:</b>       | 140 rpm          | <b>Max. Power:</b>      | 0.51 W            |
| <b>Rated Torque:</b>      | 0.23 kg.cm       | <b>Max. Efficiency:</b> | 25%               |
| <b>Termination Style:</b> | Terminals        |                         |                   |

