ISL Products International

ø22mm Planetary Gear Motor

Carbon - Brushed

MOT-IG22CGM-24V

Online ID: PGM-22C-24-246-37-02

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are equiped to handle varying loads and are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.




Contact Us for alternative solutions!


Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	27 rpm
Rated Torque:	3 kg.cm
Rated Current:	160 mA

No-Load Speed:	37 rpm (+/- 10%)
No-Load Current:	< 60 mA
Stall Torque:	18 kg.cm
Max. Power:	1.55 W
Reduction Ratio:	246:1
Termination Style:	Terminals

Dimensions



Performance Curve





 $\ensuremath{\mathbb{C}}$ 2022 ISL Products International Ltd. Specifications subject to change without notice.