



LED EP38-20W6051*e*

Bulb Class: PAR38



Product Description

LED EP38-20W6051*e* delivers superior brightness, valuable energy savings and long lasting performance. This PAR38 LED Long Neck bulb is ideal for ambient lighting or general purpose applications due to its uniform *Cool white light (5000K) and replaces conventional 150 Watt incandescent light bulbs.









\$2.40 per year





Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
20 W	120V	1700 lm	45°	N/A	5000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
80	85 lm/W	0.7	0.18 A	E26	25,000 Hrs.

Product Features

Dimmable




Energy Efficient



Damp Rated

Product Dimensions



Product Photometric Data

