


Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are equiped to handle varying loads and are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.




Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	12V DC
Rated Speed:	432 rpm
Rated Torque:	1.10 kg.cm
Termination Style:	Terminals

No-Load Speed:	529 rpm (+/- 10%)
No-Load Current:	<200 mA
Stall Torque:	5.5 kg.cm
Max. Power:	7 W
Reduction Ratio:	14:1







© 2021 ISL Products International Ltd. Specifications subject to change without notice.

ISL Products International Ltd. • 235 Robbins Ln., Ste 270 • Syosset, NY 11791 • T 516-937-3475 • www.islproducts.com