

Online ID#:

Our DC Motors are a cost-effictive solution for any application. They offer simple integration and come in a variety of sizes. With endless performance combinations, we have a tailored motor solution for you.

ISL Products International



Contact Us for alternative solutions!

Specifications	
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	4,300 rpm
Rated Torque:	274 g.cm
Rated Current:	725 mA

No-Load Speed:	5,000 rpm (+/- 10%)
No-Load Current:	<200 mA
Stall Torque:	1.8 kg.cm
Max. Power:	24 W
Termination Style:	Terminals





