

MOT-I-81343-37B

Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!



Specifications	
Gearhead Type:	Spur - Offset Shaft
Motor Type:	Carbon - Brushed
Rated Voltage:	24V DC
Rated Speed:	64 rpm
Rated Torque:	8 kg.cm
Rated Current:	600 mA

No-Load Speed:	72 rpm (+/- 10%)
No-Load Current:	< 100 mA
Stall Torque:	72 kg.cm
Max. Power:	13 W
Termination Style:	Terminals
Reduction Ratio:	120:1





