

ISL Products offers the latest technology when it comes to Coreless DC Motors. Our Coreless Brushed DC Motors offer superior performance due to a very low cogging torque resulting in higher acceleration rates.



Contact Us for alternative solutions!

Specifications	
Motor Type:	Coreless - Brushed
Rated Voltage:	24V DC
Rated Speed:	9,509 rpm
Rated Torque:	19 g.cm
Rated Current:	80 mA

No-Load Speed:	10,300 rpm (+/- 10%)
No-Load Current:	< 15 mA
Stall Torque:	247 g.cm
Max. Power:	6.5 W
Termination Style:	Terminals





