





TOLERANCES: $\pm .002$ "

SCALE 3.000

ECN NO	REVISIONS	DRN	CKD	APP	DATE
	NEW RELEASE	AJF	KLJ	NO	2-16-10

RoHS COMPLIANT 515-1061-803F

Part Numbers with the "F" suffix ending are RoHS Compliant, Packaging is marked with "RoHS Compliant" label or equivalent markings,

I. DIALIGHT PART NUMBER: 515-1061-803F.

2. COMPONENT DESIGNED TO BE PRESSED IN PCB.

3. MATERIAL TO BE CLEAR, TRANSMISSIVE POLYCARBONATE (UL 94V-0 FLAMMABILITY).

4. STORAGE AND OPERATING TEMPERATURE: -30 TO +100°C.

5. RECOMMENDED SURFACE MOUNT LEDS DIALIGHT PART NUMBERS: 597-3XXI-50XF (SINGLE COLOR) 597-77XI-50XF (BI-COLOR)

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT, REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.						
SCALE: 6.000	DRAWING NUMBER	REV				
ALL DIM'S IN; INCHES (MM)						
TOLERANCES: UNLESS OTHERWISE SPECIFIED	C - I 7 9 0 4	A				
FRACTIONS: $\pm 1/64$						
DECIMALS (,XX); ±.02 DECIMALS (,XXX); ±.015	TITLE BI-LEVEL LIGHT PIPE					
Province (, akar, 1, eres	MATERIAL					
ANGLES: ±1°	-					
FINISH:						
-	Dialight 1501 ROUTE ;					
FSCM 83330	SHEET I OF I FAMILY TABLE:					