

ø12mm Spur Gear Motor **Carbon - Brushed**

MOT-I-81548

Online ID#:


Our Spur Gear Motors are an inline solution providing ample torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.


Contact Us for alternative solutions!


Specifications	
Gearhead Type:	Spur
Motor Type:	Carbon - Brushed
Rated Voltage:	7V DC
Rated Speed:	12 rpm
Rated Torque:	616 g.cm
Rated Current:	60 mA

No-Load Speed:	15 rpm (+/- 10%)
No-Load Current:	< 30mA
Stall Torque:	2,850 g.cm
Stall Current:	225 mA
Max. Power:	0.11 W
Termination Styles:	Terminals









ISL Products International Ltd. • 572 Walt Whitman Rd., Suite 100 • Melville, NY 11747 • T 516-937-3475 • www.islproducts.com