



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT	FIGURE	CONDUCTOR RANGE	DIMENSIONS - IN [mm] ±.1 [2.5]			BOLT
PART NUMBER			L	W	Н	DIA
GM-1-Q	1	8 SOL - 4 STR	1.25 [32]	1.00 [25]	1.63 [41]	3/8"
GM-2-Q	1	4 SOL - 2/0 STR	1.63 [41]	1.13 [29]	1.75 [45]	3/8"
GM-3-Q	1	2/0 SOL - 250 kcmil	2.13 [54]	1.50 [38]	2.00 [51]	1/2"
GM-3E-X	2	4 SOL - 300 kcmil	1.96 [50]	1.50 [38]	2.32 [59]	1/2"
GM-4-X	2	300 kcmil - 500 kcmil	2.38 [60]	1.63 [41]	2.50 [63]	1/2"









NOTES:

- 1. MADE FROM HIGH COPPER CONTENT ALLOY. FURNISHED WITH FULL THREADED SILICON BOLT, NUTS, AND LOCKWASHERS.
- 2. THESE CONNECTORS ARE UL LISTED FOR GROUNDING AND BONDING, AND DIRECT BURIAL APPLICATIONS.
- 3. SEE www.PANDUIT.com FOR PACKAGE QUANTITIES.



 $DB \stackrel{\perp}{=} RATED$

							BRONZE GROUND CLAMP GM SERIES CUSTOMER DRAWING	
							ITEM REVISION NAME N41169BB/06	
							DATASET FILE NAME N41169BB-C41169/06.SLDDRW	
06	8/18	I Jhnu	JHNU	RGB	REMOVED GM-5-5, GM-6-5	N41169BB-C41169	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	
05	7/18	-	! 		ADDED GM-1-Q, GM-4-X, GM-3E-X, GM-5-5, GM-6-5	038340	.X ± .XXX ± SEE NOTES .XX ± ANGLES ±	
04	11/15	JHNU	JHNU	RGB	REVISED WIRE RANGE FOR GMS-3-Q: 2/0 SOL WAS 2/0 STR	N41169BB-C41169	THIRD ANGLE PROJECTION C41169	
REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE N/A SHEET 1 OF 1 SIZE A	