
# Hybrid Headlamp

# **Energizer**

The Energizer<sub>®</sub> High Lumen Hybrid headlamp has multiple features in a small light. It is hybrid-powered so it can be used with the rechargeable batteries that can be charged via USB as well as 2 CR123 batteries which adds a lot of flexibility to this light. In addition, this light also detaches from the band and can be used as a handheld light. The outstanding performance comes with a Turbo mode that is up to 1000 Lumens of brightness; with a simple press and hold, you'll be able to see in the darkest places. On top of all of that, its durable metal construction makes this light a very tough partner no matter the activity.

Water



Beam



#### **DESIGN BENEFITS**

- Shatterproof lens
- Detaches from base and can be used as a handheld light
- **Durable metal construction**
- Easy to use and comfortable to wear
- Compact and lightweight

#### **PERFORMANCE BENEFITS**

- Hybrid Powered: rechargeable (USB) or 2 CR123s
- ✓ Turbo mode: 1000 Lumens (press and hold)

## **LIGHT AND POWER SOURCE**

PRODUCT SPECIFICATIONS

- ✓ Works with either removable rechargeable lithium ion battery or 2 CR123 batteries
- Rechargeable battery fully charges in 5 hours.

# BATTERY SPECIFICATIONS Rechargeable li-ion 18650 2000mAH

1 **Number of Cells** BATTERY PERFORMANCE

TROBOCT STEELINGATIONS				
Weight:	55 Grams / 1.94 Ounces			
Dimensions:		27.5 mm x 25.5 mm x 106.5 mm		
		1.08" x 1.00" x 4.19"		
ELECTRICAL CHARACTERISTICS				

	Lumens	Runtime	Beam Distance		
	(lm)	(h)	(m)		
	400	4.5	50		
	185	8	45		
	30	55	18		
	1000		100		

Nominal Power Consumption: 9.62 W

Batteries: Li-ion rechargeable battery 2000 mAH 3.7V

LED Specifications: LED 3.0V cc / 3360 mA

## **DISCLAIMERS**

Tested according to ANSI FL1 Standards.

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

# **BATTERY SPECIFICATIONS**

**Energizer Lithium Battery Type Battery Size** 

CR123 **Number of Cells** 2

**Battery Type** 

**Battery Size** 

Modes

Medium

High

Low

Low

Turbo

Turbo

BATTERY PERFORMANCE

**Beam Distance Modes Runtime** Lumens (lm) (h) (m) 50 High 400 4.5 Medium 185 8 45

20

Modes

High, Medium, Low, Turbo, Strobe

30

1000

## **EMERGENCY STROBE WARNING**

A small percentage of people may experience a seizure when exposed to certain visual images, including flashing lights and strobing lights.

### **CERTIFICATES AND COMPLIANCE**

EMC, EN62471, FCC

Publish Date: 10-22-2020

Before using your flashlight, please read all instructions and cautionary marking on the package and the light. This datasheet contains information specific to products manufactured at the time publication. Contents do not constitute a claim or warranty. ©2020 Energizer

18

100