




REV.	EN. NO.	DESCRIPTION	SIGN	DATE
C1	N/A	INITIAL DRAWING	Victory	2019/08/20



21XXX211-01
Pin Number

7 Pin	P/N: 21007211-01	8 Pin	P/N: 21008211-01
5 Pin	P/N: 21005211-01	6 Pin	P/N: 21006211-01

Pin Assignments Front View



- Specification:
1. Operation Temperature: -45°C~105°C.
 2. Insulation Resistance: 100M Ω at DC 500V.
 3. Contact Resistance: <10m Ω
 4. Withstand Voltage: 1300V AC.
 5. Operating Current: 2A.
 6. Operating Voltage: AC 50V.
 7. Waterproof Rate: IP67 (Mated).
 8. Connector: Nylon+GF, Black.
 9. Seal Nut: Nylon, Black.
 10. O-Ring: Silicon, Red.
 11. Clamp Ring: Nylon, Black.
 12. Gasket: Silicon, Red.
 13. Female Pin: Copper Alloy, Gold Plated.
 14. RoHS Compliant.
 15. UL Compliant.
 16. Cable Range OD: $\phi 4.7$ mm~ $\phi 6.2$ mm
 17. Mating Cap P/N: 111-00053-00.

UNIT: mm	DESCRIPTION
TOLERANCE	Mini Series Screw Type
.X	Male Plug With Female Pin
.XX	SCALE: 1:1
.XXX	SCALE: 1 OF 1
ANGLES	REVISION: C1
	SIZE: A4
	SHEET: 1
	*: Inspection Item

CHOGORI

PART NO	21XXX211-01	DRAWN BY	Victory	DATE	2019/08/20
DWG NO		CHECKED BY	Ivan	DATE	2019/08/20
CUSTOMER		APPROVED BY	Ponson	DATE	2019/08/20