


Molex Part Number	DIM A Overall Length (in[mm])	Braid Type	Approx. Circular Mills	Ampacity Max	Approx. AWG Equivalent	DIM B Terminal Width (in[mm])	DIM C Terminal Thickness (in[mm])	DIM D Terminal Length (in[mm])	DIM E Terminal Hole Dia (in[mm])	DIM F C/L of Terminal Hole (in[mm])
2076025016	6.0 [152]	24x5/30	12060	53	10	.540 [13.72]	.080 [2.03]	.440 [11.21]	.203 [5.16]	.260 [6.60]
2076025017	12.0 [305]									
2076025018	18.0 [457]									
2076025019	24.0 [607]									
2076025020	36.0 [914]									
2076025021	6.0 [152]	48x24/36	28800	105	6	.750 [19.05]	.095 [2.41]	.670 [17.05]	.281 [7.14]	.375 [9.53]
2076025022	12.0 [305]									
2076025023	18.0 [457]									
2076025024	24.0 [607]									
2076025025	36.0 [914]									
2076025026	6.0 [152]	48x14/30	67200	150	2	1.00 [25.4]	.120 [3.05]	.920 [23.4]	.406 [10.31]	.500 [12.70]
2076025027	12.0 [305]									
2076025028	18.0 [457]									
2076025029	24.0 [607]									
2076025030	36.0 [914]									



FOR INFORMATION USE ONLY

- NOTES:
- MATERIAL:
 - FERRULES - COMPRESSED SEAMLESS COPPER TUBE
 - BRAID - ELECTRO-PLATED TIN COPPER
 - HEAT SHRINK TUBING - VW-1, 600V, 125°, COLOR: BLACK
 - .005 [0.13] MAX BURR ON ALL SURFACES
 - MOLEX LOGO "MX" SHALL BE STAMPED INTO THE PART, LOCATED APPROXIMATELY AS SHOWN AND BE LEGIBLE.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS: HYBRID		SCALE: 1:2		CURRENT REV DESC:											
GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± °		EC NO: 2019/09/23											
4 PLACES ±		3 PLACES ±		DRWN: TGREGORI				FLEXIBLE BRAIDED GROUND STRAPS WITH INSULATION							
2 PLACES ±		1 PLACE ±		CHK'D:				PRODUCT CUSTOMER DRAWING							
0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING: B-SIZE		SERIES: 207602		MATERIAL NUMBER: SEE TABLE		CUSTOMER: GENERAL MARKET		SHEET NUMBER: 1 OF 1	
APPR:		INITIAL REVISION:		2019/08/15				DOCUMENT NUMBER: 2076020001-SD		DOC TYPE: PSD		DOC PART: 000		REVISION: 2	