


AST-118 Close-Up



AST-10 Close-Up



The **AST-118** and **AST-10** are designed to gain mid span access by slitting open jacketed and jacket & armored fiber optic cables. The tools have an adjustable depth precision made blade that will cut through the toughest material while insuring no damage to the fibers. The tools can be set for Longitudinal cuts as well as radial cuts. Replacement blade: **AST-RB**

SPECIFICATIONS	AST-10	AST-118
CUT TYPE	Slit, Ring	Slit, Ring
CABLE TYPE	Armored, Jacket	Armored, Jacket
CABLE DIAMETER	4 mm-10 mm (0.157"-0.393")	8 mm-28.6 mm (0.315"-1.125")
LENGTH	5.125" (130.175 mm)	5.125" (130.175 mm)
WEIGHT	0.685 lbs (0.31 kg)	0.685 lbs (0.31 kg)
UPC #	811490019546	811490019553

MADE FOR LIFE®