



LED EB30-11W3050*e*

Bulb Class: BR30



Product Description

LED EB30-11W3050*e* replaces conventional 65 Watt incandescent bulbs delivering more brightness (lumens) for less energy (Watts). With lower energy consumption levels you will be able to experience considerable energy savings throughout the years. EB30-11W3050 \emph{e} design reduces internal bulb heat providing greater durability and constant bulb performance.








Estimated Energy Cost:

\$1.32 per year





Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
11 W	120V	850 lm	110°	N/A	5000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
80	77.3 lm/W	0.7	0.13 A	E26	25,000 Hrs.

Product Features



Dimmable




Energy Efficient



Damp Rated

Product Dimensions



Product Photometric Data

