



LED EB40-11W5040*cec*

Bulb Class: BR40



90⁺ True COLOR

Product Description

LED EB40-11W5040cec delivers superior brightness, valuable energy savings, long lasting performance and true color perception. This BR40 LED flood bulb is ideal for ambient lighting due to its uniform *Bright white light (4000K) and replaces conventional 80 Watt incandescent light bulbs. Enjoy features such as: Instant on, dimming options, energy efficient, 90+CRI, and damp rated.










Estimated Energy Cost: \$1.32 per year







Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
11 W	120V/60Hz	1000 lm	110°	N/A	4000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
90	91 lm/W	0.9	0.1 A	E26	25,000 Hrs.

Product Features



Dimmable




Energy Efficient



Damp Rated

Product Dimensions



Product Photometric Data

