




LED AUTO OR TRUCK LIFT KIT



Model Number	Nominal Power LED	Strips Qty Listed	Ambient Lumens*	DLC reported Lm/w
LED Lift Kit	30W 30W	2 x 42" 2 x 21"	8800	147

Optilumen LED Auto or Truck Lift Kit removes the hassle of moving the trouble light around your work area.

Super simple installation in 3 easy steps: 1). Attached magnetically backed strips—the long strips on each of the columns and short strips on each of the arms. 2). Quick connect the wiring harnesses and install cover. 3). Plug in the drivers.

Clean up is easy too. You can remove the magnetic strips and power supply to remove debris from the lift.

SEE WHAT YOU'RE WORKING ON





* Test results verified by UL Verification Services Inc.

LED AUTO OR TRUCK LIFT KIT



- Each LED Lift Kit includes four 4 ft. LED magnetic strips with clear snap on lens covers, two 2 ft. LED magnetic strips with clear snap on lens covers, two 30-Watt drivers, two 6 ft. quick connect leads to the strips
- Perfect for cold start applications down to -49°F and as high as 158°F
- · LED strips and driver are backed with rare earth magnetic tape, mounts to the lift in seconds
- CRI of 82
- Accepts 120 to 277-volt
- Power factor of up to .989
- · Snap on lens covers keep LED strips free from debris
- Suitable for damp locations.