

# Han 1A-M12-f D-coded, latch



Part number	09 10 004 3100
Specification	Han 1A-M12-f D-coded, latch
HARTING eCatalogue	https://b2b.harting.com/09100043100

Image is for illustration purposes only. Please refer to product description.

## Identification

Category	Inserts
Series	Han <sup>®</sup> 1A

#### Version

Termination method	Crimp termination
Gender	Female
Locking type	Snap-in latches
Size	1 A
Shielding	With cable tie
Number of contacts	4
further contacts	+ shielding
Details	Please order crimp contacts separately.  Order separately the hoods/housings for an IP65 performance.  Contact insert not compatible with 09 10 000 0800 (bulkhead mounted housing, angled)
Details	A Han <sup>®</sup> 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector. In this case protection against electric shock must be provided by the installation methods of the user.  Contact inserts must not be coupled or decoupled under electrical load.  Contact inserts must not be powered-up in the un-mated condition.

#### Technical characteristics

Conductor cross-section	0.13 0.82 mm²
Rated current	4 A
Rated voltage	48 V AC
	60 V DC

Page 1 / 3 | Creation date 2021-03-04 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany

Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

This product is not orderable anymore. Contact your local distribution partner for alternatives.



## Technical characteristics

Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	100 Mbit/s
Insulation resistance	>10 <sup>8</sup> Ω
Limiting temperature	-30 +90 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP20

# Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

# Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3 EN 45545-2 R23: HL1, HL2, HL3 EN 45545-2 R24: HL1, HL2, HL3 IEC 61373 Category 1 Class B EN 60664-1
Approvals	DNV GL

#### Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Romania
European customs tariff number	85366990

Product data sheet 09 10 004 3100 Han 1A-M12-f D-coded, latch

This product is not orderable anymore. Contact your local distribution partner for alternatives.



## Commercial data

eCl@ss

27440205 Contact insert for industrial connectors