

Datasheet for part number DAM15PSK87

Our Catalog Part Number: DAM-15P-S-K87

Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*M

| Product Datasheet | |
|---------------------------------|------------------------------------|
| General | D*M High reliable D-Sub Connectors |
| Wire Gauge Range AWG | AWG 20-28 |
| Mating Cycles | 200 |
| Contact Arrangement | 15 contacts size 20 |
| Dielectric Withstanding Voltage | 1000 VAC at sea level |
| Current Rating | 7.5 A max |
| Contact Resistance | 7.5 milli Ohm max |
| Operating Temperature | -55°/+125° |
| Salt Spray Test | 20 hours |
| Shell Material | steel |
| Shell Finish | pur tin over nickel |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | black |
| Gender | Pin |
| Contact Type | Right angled PCB |
| Contact Material | copper alloy |
| Contact Finish | gold over nickel |
| Hardware | .120" (3,05mm) Through Hole |