

Onanon Connector Series MagConnect[™] | Echo

Onanon's *MagConnect*[™] | *Echo* is performance engineered to be the most intuitive interconnect in the world. Its unique magnetic safety latch feature is ideal for medical applications, where time, precision, and quality are most critical. Additional suitable markets include but are not limited to the automotive, aerospace and industrial industries. MagConnect[™] series has been used in applications with low & high voltages, sensitive EMI, shock & vibration environments, and integration of intelligent electronics.

- 2 to 20 pin capacity
- Intuitive and self-mating
- Magnetic safety de-latching
- Customizable for reusable or single use applications
- Easily add components such as EEPROMs, resistors and capacitors
- EMI/RFI Safe
- Low (<12v) & High (>5000v) Voltage Safe
- Rugged use in outdoor wearables
- VF/HF/RF Safe

ensitive EMI, shock on of intelligent Options To Add Your Logo Here

Specifications

Mechanical

Mating Type: Magnetic Mating Cycles: 10k Min. Mating Forces:

Insertion: Magnetic Removal: 3.5 lbf Min.

Electrical

Operating Voltage: 1kVAC and 1.5kVDC Operating Current: 3A

Environmental

Sterilizable: Gamma, EtO **Chemical Resistance:** Common

cleaning solvents

Finger Safety: IEC 60601-1 Storage & Operating Temp:

0-150°C

Compatibility


Contacts: 20 pins
Plug Cable Assembly

Accepted Wire Gauges: 26-50 AWG

Cable Jacket OD: 0.286" Max Contact Termination: Solder




Onanon Connector Series MagConnect[™] | Echo




Dimensions






Recommended Cable




Contact Sales for unspecified dimensions.


Panel Mount Receptacle PN: 234-A002




Recommended PCB or Flex Dimensions



Reversable Panel Nut



Recommended Panel Cutout



Materials & Assembly

Plug Assembly

Plug Housing: Thermoplastic Polyester Retaining Cap: Thermoplastic Polyester Male Pins: Gold Plated Brass Allov Magnet: Nickel Plated Neodymium

Slip-On Boot: Thermoplastic Polyurethane

Required Assembly: Assemble connector

body after terminating wires

Panel Mount Receptacle

Insulator Insert: Thermoplastic Polyester Metal Shell: Chromium Plated Brass Alloy Female Pins: Gold Plated Brass Allov Magnet: Nickel Plated Neodymium

Required Assembly: Solder a PCB or flex

assembly

Contact Us: sales@onanon.com | (408) 262-8990 | www.onanon.com