



# DUALSLIM CAT.6 RJ45 FEEDTHROUGH CONNECTOR

Can be front or rear mounted in the panel





#### **VARIANTS**

Part No.

CP30722 DUALSLIM Cat.6 RJ45 Black plastic frame, CSK holes

CP30722X DUALSLIM Cat.6 RJ45 Black plastic frame, Ø2.5 PLAIN holes DUALSLIM Cat.6 RJ45 Black plastic frame, Ø3.2 PLAIN holes

Ø3.2mm CSK 90° x Ø5.85 'X' PLAIN Ø2.5 HOLES

'X1' PLAIN Ø3.2 HOLES

### Feedthrough Features

- Fits standard rectangular cutout.
- Front or rear mounting through the panel.
- Various hole mounting options.
- No soldering or punch termination. Use standard cable for each connector style.
- Low rear profile.

## General:

Please note: Functionality is affected by cable quality, length and cable wiring configuration.

#### Material:

- 1. RJ45 In-Line Coupler: ABS UL94-V0
- 2. RJ45 In-Line Coupler Contact:

Phosphor Bronze, 3-50 micro inches gold plating over nickel plate.

- 3. PCB: FR4
- 4. Frame: Polyamide UL94-V2

# Performance:

- 1. T568A & T568B wiring.
- 2. Meet ISO/IEC 11801 and EN50173
- 3. Meet ANSI/TIA/EIA 568B.2
- 4. Rating: 125VAC RMS 1.5A
- 5. Operating Temperatures: Min -10°C Max +60°C

For further information, contact sales@cliffuk.co.uk

# **Cliff Electronic Components Limited,**

76 Holmethorpe Avenue, Holmethorpe Ind. Estate, Redhill, Surrey RH1 2PF U.K.

Tel: +44 (0)1737 771375 Fax: +44 (0)1737 766012





www.cliffuk.co.uk

© CLIFE 04/2022 ISS 2