12 WATT LED BLACK TASK LIGHT, 18"

95803 18" Long, 12 Watt LED Black Flexible Arm Lamp, Magnetic Base





ARM LENGTH	18" (457.2mm)
ARM MATERIAL	Steel
OUTSIDE DIAMETER	.640"
COVERING SLEEVE	PVC, Gloss Black
BULB	Installed, non integrated 12 watt (1100 Lumen), A19 size, LED bright white bulb (75 watt equivalent)
SHADE/REFLECTOR	5.75" high, 4.5 diameter, rotates 270°, Bright conical reflector puts light where you need it
SWITCH	Toggle style
CORD	3-wire 18 gauge SJTO, rated 105°C, with NEMA 5- 15P 3 prong grounded plug
APPROVALS	C-UL listed
MOUNTING	Magnetic base 100lb pull, 3" diameter
BASE	Direct mount base of arm mounts to magnetic base with two 1/4-20 socket head cap screws

800-346-0761

222 Cessna Street

Watertown, SD 57201

sales@moffattproducts.com

moffatt