

Datasheet for part number DCM21WA4SA191A197

Our Catalog Part Number: DCM-21WA4S-A191-A197		
Our Global Manufacturing Part Number: 115267-1543 D		
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D		

Product Datasheet	
General	Combo D Series: D-Subminiature offering mixed layouts
Wire Gauge Range AWG	AWG 8-26
Mating Cycles	200
Contact Arrangement	21WA4 (17 contacts size 20, 4 empty size 8 cavities)
Dielectric Withstanding Voltage	500 VAC at sea level
Current Rating Signal Contacts	7.5 max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Socket
Contact Type	Solder pot
Contact Material	copper alloy
Contact Finish	gold over nickel (Performance Class 2)
Mounting Method	.120" (3,05mm) Through Hole