
HEAVY DUTY GOOSENECK FLEX ARM

95154 16" Long, 1/4-20 Female, C-Clamp Base



ARM LENGTH	16" (406.4mm)
ARM MATERIAL	Steel
OUTSIDE DIAMETER	.695"
INSIDE DIAMETER	.325"
LOAD RATING	Max Load @ 90 Degrees:
	2.5 pounds
FEEL	Heavy Duty, Feels Stiff
MOUNTING STYLE	C-Clamp, 2.5" L x 2.0" W x 1.5" H
	Threaded in place with Loctite
TOP FITTING	1/4-20 UNC Female Thread
	Male Thread Conversion Kit included with single
	use tube of Loctite and Male Stud
BASE FITTING	Black e-coated 3/8 NPSM x .375" long Hex Ferrule
COVERING SLEEVE	PVC, Matte Black





800-346-0761

222 Cessna Street
Watertown, SD 57201
sales@moffattproducts.com

