TI Home > Semiconductors > Analog & Mixed-Signal > Power Management > Switching Regulator > DC/DC Converter (Integrated Switch) > Step-Down Regulator >

▼ Worldwide (In English)

### 36 Volt Simple Switcher® Module 10A Demo Board Status: ACTIVE

## LMZ13610DEMO



Description/Features

Technical Documents

Support & Community

Order Now

### Description

The LMZ13610 SIMPLE SWITCHER® power module is an easy-to-use DC-DC solution capable of driving up to a 10A load. They are available in an innovative package that enhances thermal performance and allows for hand or machine soldering.

The LMZ13610 can accept an input voltage rail between 6V and 36V. The device can deliver an adjustable and highly accurate output voltage as low as 0.8V and as high as 6V. The control structure is constant frequency PWM. The control loop operates well with low ESR output capacitors such as ceramics. The precision enable input allows for programmable UVLO of the input supply. The external soft-start capacitor facilitates a controlled and adjustable startup rise time of the output. The LMZ13610 family is a reliable and robust solution with the following features: loss-less cycle-by-cycle valley current limit to protect for over current or short-circuit fault, thermal shutdown, input under-voltage lockout, and will start up into a pre-biased output. Free-running switching frequency is 350 kHz.

### Features

V<sub>IN</sub> = 6V to 36V Enable UVLO = 5.7V  $V_{OUT} = 5V$ , 3.3V, 2.5V, 1.2V  $I_{OUT} = 0$  to 10A  $?J_{A} = 9.9$ °C / W,  $?_{JC} = 1.0$ °C/W PCB designed on four layers Inner are 1 oz. Outer are 2 oz. Measures 3.0 in. x 3.5 in. (7.5 cm x 8.9 cm) 62mil (.062 inch) thick of FR4 laminate material Max ambient temp of 65°C at full 10A load, no airflow measured at 12 V<sub>IN</sub>

LMZ13610 10A SIMPLE SWITCHER Power Module with 36V Maximum Input Voltage Demonstration Board



## Order Now

Part Number	Texas Instruments	Status	
LMZ13610DEMO: 36 Volt Simple Switcher® Module 10A Demo Board	Order Online	ACTIVE	

### **Related Products**

TI Devices

Part Number Name

Product Family

LMZ13610 10A SIMPLE SWITCHER® Power Module with 36V Maximum Input Voltage Integrated Power Solutions

# Support and Community

Customer Tags

No Tags are Available for this Part Number

Other Support

TI E2E Community Contact Technical Support <u>Training</u>