HEAVY DUTY GOOSENECK FLEX ARM

95132 9" Long, 1/4-20 Female Both Ends



ARM LENGTH	9" (228.6mm)
ANVILLINGTTI	9 (228.011111)
ARM MATERIAL	Steel
OUTSIDE DIAMETER	.695"
INSIDE DIAMETER	.325"
LOAD RATING	Max Load @ 90 Degrees:
	3.5 pounds
FEEL	Heavy Duty, Feels Stiff
MOUNTING STYLE	Female Threads, or
	Male Thread Conversion Kit included with single
	use tube of Loctite and Male Studs (2)
TOP FITTING	1/4-20 UNC Female Thread
BASE FITTING	1/4-20 UNC Female Thread
COVERING SLEEVE	PVC, Matte Black



800-346-0761

222 Cessna Street
Watertown, SD 57201
sales@moffattproducts.com

