

Technical Data Sheet

50W PoE to USB-C PD Power Adapter, 802.3 BT Compliant

Model Number: CG-PoE-CESBT

Rev 01.201223



G-POE-CESBT is an indoor PoE rated networking converter, designed to convert PoE to Type-C PD. Features 1 PoE port for 802.3bt standard input, 1 Type-C port for power output and 1 RJ45 port for data output.

Features

- Indoor PoE rated networking converter, designed to convert
- PoE to Type-C PD
- Data Speed: 10/100/1000Mbps
- Input: 44-57Vdc IEEE802.3bt
 - Output: 5V/9V/12V/15V/20V (5V/3.4A, 9V/3A, 12V/3A,
- 15V/3A, 20V/2.5A)
- **Poe Injector not included Customer Supplied**

Product Information

- Model Number: CG-PoE-CESBT
- Packing List: 1x PoE to USB-C PD Power Adapter

2 | TECHNICAL DATA SHEET



Specifications

OVERVIEW

Product Type	Splitter
USB Specification	Charging Only
Maximum Data Rate	10/100/1000Mbps
Mountable	Desktop
Compliance	IEEE 802.3 bt

CONNECTIONS

Downstream Port Count	1
Downstream Port Type	RJ-45
Power Input	44V ~ 57V

ENVIRONMENTAL

Operating Temperature	10C ~ 60C	
Operating Humidity	N/A	

DIMENSIONS

Length	3.54331 inches
Width	2.52835 inches
Height	0.94488 inches

OS SUPPORT

|--|

WARRANTY

Warranty Period	1 Year

PRODUCT URL

CG-PoE-CESBT Product Page	https://www.coolgear.com/product/poe-to-type-c-pd-splitter-bt

© 2020 Coolgear, Inc. All Rights Reserved. All products and accompanying digital documentation including images are the property and / or trademarks of Coolgear Inc. Coolgear Inc. are continuously improving upon its products. Product specifications are subject to change without notice

Coolgear, Inc.

5120 110th Ave N

P: +1-727-209-1300

F: +1-727-209-1302 Clearwater, FL 33760 USA www.coolgear.com